



Main

Range of product	Stago
Product or component type	Cover clamp
Device short name	H60
Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards

Complementary

Product destination	Cable tray KG281 60 mm height and Cable tray KB184 60 mm height and Cable tray KB284 60 mm height and Cable tray TV184 60 mm height and Cable ladder LB4000 60 mm height and Cable ladder WHS 60 mm height and
Fixing mode	Screwless
Material with surface treatment	Stainless steel AISI 301
Corrosion class	C5-I
Height	68 mm
Width	23 mm
Depth	21 mm
Product weight	0.008 kg / set of 20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1152 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

