

Product data sheet

Characteristics

CSU76602034

Stago - ES114 tray closed 60x200mm L=3m 1mm stainless steel AISI 304



Main

Range of product	Stago
Product or component type	Cable tray
Cable support type	Unperforated
Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards

Complementary

Product destination	ES114 cable tray
Fixing mode	By screw
Material with surface treatment	Stainless steel AISI 304
Corrosion class	C5-I
Thickness	1 mm
Nominal cross section	12000 mm ²
Height	60 mm
Width	200 mm
Length	3000 mm
Product weight	2.7 kg / 100 m

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1833 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications