



## Main

Range of product	Stago
Product or component type	Cable tray
Cable support type	Unperforated
Mounting location	For area with almost permanent high levels of humidity, airborne pollution and salt, such as purify-ing plants and offshore

## Complementary

Product destination	ES114 cable tray
Fixing mode	By screw
Material with surface treatment	Stainless steel AISI 316
Corrosion class	C5-M
Thickness	1 mm
Nominal cross section	12000 mm <sup>2</sup>
Height	60 mm
Width	200 mm
Length	3000 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications