

# Product data sheet

Specifications



## Stago - horizontal bend 90° formed 60x400mm stainless steel AISI 316

CSU76624040

⚠ Discontinued on: Sep 19, 2018

⚠ Discontinued

### Main

Range Of Product	Stago
Product Or Component Type	Bend

### Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Inner Radius	100 mm
Adjustment	Fixed
Product Destination	Cable tray ES114 H= 60 mm W= 400 mm
Fixing Mode	By screw
Material With Surface Treatment	Stainless steel AISI 316
Corrosion Class	C5-M

### Environment

Mounting Location	Area with almost permanent high levels of humidity, airborne pollution and salt purifying plants and offshore
-------------------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications