


# Product data sheet

Specifications



## Stago - t-piece formed 60x120mm stainless steel AISI 316

CSU76631240

 **Discontinued on:** Sep 19, 2018

 **Discontinued**

### Main

Product Or Component Type	T-piece
---------------------------	---------

### Complementary

Operating Angle	90 °
Direction Change Type	Vertical
Adjustment	Fixed
Product Destination	Cable tray ES114 H= 60 mm W= 120 mm
Fixing Mode	By screw
Material	Stainless steel AISI 316
Inner Radius	100 mm
Height	63 mm
Width	526 mm
Depth	325 mm

### Environment

Atmospheric-Corrosivity Category	C5-M
Environmental Characteristic	Area with almost permanent high levels of humidity, airborne pollution and salt purifying plants and offshore

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications