



Main

Product or component type	T-piece
---------------------------	---------

Complementary

Operating angle	90 °
Direction change type	Vertical
Adjustment	Fixed
Product destination	Cable tray ES114 height 60 mm width 600 mm
Fixing mode	By screw
Material	Stainless steel AISI 316
Inner radius	100 mm
Height	60 mm
Width	840 mm
Depth	720 mm

Environment

Atmospheric-corrosivity category	C5-M
Environmental characteristic	Area with almost permanent high levels of humidity, airborne pollution and salt purify-ing plants and offshore

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications