



Main

Range of product	Stago
Range	Stago
Product or component type	Riser

Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	120 mm
Adjustment	Fixed
Product destination	ES114 cable tray 60 mm height and 330 mm width
Fixing mode	By screw
Corrosion class	C5-I
Thickness	1 mm
Height	300 mm
Width	333 mm
Depth	300 mm
Product weight	1.9 kg / set of 100

Environment

Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards
-------------------	--

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications