



### Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Reinforced cable ladder
Device short name	KHZP 20C
Device application	Industrial application

### Complementary

Type of side profile	Closed profile
Type of rung	Perforated profile
Mounting location	Indoor Outdoor
Rung spacing	250 mm
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Height	190 mm
Width	297 mm
Length	6 m
Product weight	900 kg / 100 m

### Environment

Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants
Standards	NEMA 20C IEC 61537