



Main

| | |
|---------------------------|-------------------------|
| Range | Wibe |
| Product name | Wibe Cable Ladders |
| Product or component type | Reinforced cable ladder |
| Device short name | KHZP 20C |
| Device application | Industrial application |

Complementary

| | |
|---------------------------------|---------------------------|
| Type of side profile | Closed profile |
| Type of rung | Perforated profile |
| Mounting location | Indoor Outdoor |
| Rung spacing | 250 mm |
| Material with surface treatment | Steel, hot-dip galvanized |
| Corrosion class | C3/C4 |
| Height | 190 mm |
| Width | 497 mm |
| Length | 6 m |
| Product weight | 967 kg / 100 m |

Environment

| | |
|-------------------|---|
| Mounting location | For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants |
| Standards | NEMA 20C IEC 61537 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications