



Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Reinforced cable ladder
Device short name	KHZP 20C
Device application	Industrial application

Complementary

Type of side profile	Closed profile
Type of rung	Perforated profile
Mounting location	Indoor Outdoor
Rung spacing	250 mm
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Height	190 mm
Width	797 mm
Length	6 m
Net weight	1033 kg / 100 m

Environment

Mounting location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants
Standards	NEMA 20C IEC 61537

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications