



Main

Range of product	Wibe Cable Ladders
Device short name	20C
Product or component type	90° interior bend

Complementary

Direction change type	Horizontal
Inner radius	268 mm
Type of rung	Perforated profile
Product destination	Reinforced cable ladder 397 mm width
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Height	190 mm
Width	825 mm
Depth	825 mm
Net weight	700 kg / set of 100

Environment

Mounting location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants
Standards	NEMA 20C