

Product data sheet

Specifications



Wibe - 90° interior bend 20C-800 - steel hot-dip galvanized

CSU795150

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

| | |
|---------------------------|--------------------|
| Range Of Product | Wibe Cable Ladders |
| Device Short Name | 20C |
| Product Or Component Type | 90° interior bend |

Complementary

| | |
|---------------------------------|--------------------------------------|
| Direction Change Type | Horizontal |
| Inner Radius | 268 mm |
| Type Of Rung | Perforated profile |
| Product Destination | Reinforced cable ladder 797 mm width |
| Material With Surface Treatment | Steel, hot-dip galvanized |
| Corrosion Class | C3/C4 |
| Height | 190 mm |
| Width | 1225 mm |
| Depth | 1225 mm |
| Net Weight | 700 kg / set of 100 |

Environment

| | |
|-------------------|---|
| Mounting Location | Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants |
| Standards | NEMA 20C |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 19 cm |
| Package 1 Width | 122.5 cm |
| Package 1 Length | 122.5 cm |
| Package 1 Weight | 8.238 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications