

Product data sheet

Specifications



Wibe - T-junction 20C-400 - steel hot-dip galvanized

CSU795154

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range	Wibe
Range Of Product	Wibe Cable Ladders
Product Or Component Type	T-junction
Device Short Name	20C

Complementary

Inner Radius	268 mm
Type Of Side Profile	Closed profile
Type Of Rung	Perforated profile
Product Destination	Reinforced cable ladder 397 mm width
Material With Surface Treatment	Steel, hot-dip galvanized
Corrosion Class	C3/C4
Length	1250 mm
Height	190 mm
Width	825 mm
Net Weight	900 kg / set of 100

Environment

Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants
Standards	NEMA 20C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19 cm
Package 1 Width	82.5 cm
Package 1 Length	125 cm
Package 1 Weight	8.999 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications