



### Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Cable ladder
Device short name	KHZSPZ
Device application	Industrial application

### Complementary

Type of side profile	Open profile
Type of rung	Perforated profile
Mounting location	Indoor Outdoor
Rung spacing	250 mm
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Height	55 mm
Width	598 mm
Length	3000 mm
Product weight	280 kg / 100 mm

### Environment

Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants
Standards	IEC 61537

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications