



## Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Cable ladder
Device short name	KHZSP
Device application	Industrial application

## Complementary

Type of side profile	Open profile
Type of rung	Perforated profile
Mounting location	Outdoor Indoor
Rung spacing	250 mm
Material with surface treatment	Stainless steel 304L
Corrosion class	C5-M
Height	55 mm
Width	298 mm
Length	3 m
Product weight	217 kg / 100 m

## Environment

Mounting location	For area with almost permanent high levels of humidity, airborne pollution and salt, such as purify-ing plants and offshore
Standards	IEC 61537