



Main

Product or component type	Branching piece
---------------------------	-----------------

Complementary

Operating angle	90 °
Direction change type	Horizontal
Shape	U-shape
Adjustment	Foldable
Fixing mode	Screwless
Material	Steel with zinc+
Height	85 mm
Width	500 mm

Environment

Standards	EN/ISO 9227
-----------	-------------