

Product data sheet

Specifications



10AX 250V Surface Mount One Gang Two Way Switch IP66

CSW110

Main

Range	Kavacha
Product Or Component Type	Switch
Device Short Name	AS

Complementary

Wiring Device Mounting	Surface
Switch Function	2-way switch with looping terminal
Rated Current	10 AX at 250 V AC
Number Of Gangs	1 gang
Width	80 mm
Height	103 mm
Depth	65 mm

Environment

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP66
Standards	BS EN 60669-1 : 2000 IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	10.3 cm
Package 1 Length	6.5 cm
Package 1 Weight	0.001 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	End of Life Information