



Main

Range	Kavacha
Product or component type	Switch
Device short name	AS

Complementary

Wiring device mounting	Surface
Switch function	2-way switch with looping terminal
Local signalling	Indicator light neon (red)
Rated current	20 A at 250 V AC 16 AX at 250 V AC
Number of gangs	2 gangs
Width	80 mm
Height	103 mm
Depth	65 mm

Environment

Environmental characteristic	Weatherproof
IP degree of protection	IP66
Standards	IEC 60529 BS EN 60669-1 : 2000

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications