

Product data sheet

Specifications



DIN cartridge fuses, TeSys GS,
blade size DIN NH4, fuse type gG,
500VAC, 1000A, without striker, set
of 1 part

DF2LN1101

! Discontinued

! Discontinued on: Feb 1, 2021

Main

Range Of Product	DF
Range	TeSys
Product Or Component Type	Fuses
Device Short Name	blade fuse
Device Application	Protection
[Ue] Rated Operational Voltage	500 V AC
Fuse Size	NH4
Fuse Type	DIN

Complementary

[In] Rated Current	1000 A
Fuse Curve	GG
Quantity Per Set	Set of 1
Net Weight	1.9 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov