



Main

| | |
|---------------------------|---|
| Range of product | Digilink |
| Product or component type | Fibre optic cable multi mode |
| Optic fibre type | Non armoured for indoor/outdoor application |

Complementary

| | |
|-----------------------|-----------------------|
| Fibre performance | OM3 |
| Optic fiber core | 50 µm |
| Condition of use | Indoor/outdoor |
| Cable weight | 90 kg/km |
| Bending radius | 20 x overall diameter |
| Number of optic fibre | 4 |
| Tensile strength | 2670 N |
| Crush resistance | 0.044 N/m |

Environment

| | |
|---------------------------------------|--------------------------------|
| Ambient air temperature for operation | -30...70 °C |
| Ambient air temperature for storage | -40...75 °C |
| Standards | ISO/IEC 11801 TIA/EIA-568-B |

Offer Sustainability

| | |
|----------------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 1736 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|