

Product data sheet

Specifications

Unitube, Light-Armoured Cable, Multi-Mode, 6 Core, 62.5um



DFXAO62GCT06

⚠ Discontinued on: Dec 30, 2016

⚠ End-of-service on: Dec 30, 2019

⚠ Discontinued

Main

Range Of Product	Digilink
Product Or Component Type	Fibre optic cable multi mode
Optic Fibre Type	Light armoured (outdoor - duct, aerial, direct buried)

Complementary

Optic Fiber Core	62.5 µm
Condition Of Use	Outdoor
Cable Weight	90 kg / 1 km
Bending Radius	20 x overall diameter
Number Of Optic Fibre	6
Tensile Strength	1000 N
Crush Resistance	0.044 N/m

Environment

Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...75 °C
Standards	ISO/IEC 11801 TIA/EIA-568-B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	1 cm
Package 1 Length	100 cm
Package 1 Weight	80 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications