



Main

Range of product	Digilink
Product or component type	Fibre optic cable multi mode
Optic fibre type	Light armoured for outdoor - duct, aerial, direct buried application

Complementary

Optic fiber core	62.5 µm
Condition of use	Outdoor
Cable weight	90 kg/km
Bending radius	20 x overall diameter
Number of optic fibre	12
Tensile strength	1000 N
Crush resistance	0.044 N/m

Environment

Ambient air temperature for operation	-30...70 °C
Ambient air temperature for storage	-40...75 °C
Standards	ISO/IEC 11801 TIA/EIA-568-B

Contractual warranty

Warranty period	18 months
-----------------	-----------