

Product data sheet

Specifications

ST Connector, Multi-Mode, 0.9mm



DFXOSTXMPR09

⚠ Discontinued on: Dec 31, 2018

⚠ Discontinued

Main

Range Of Product	Digilink
Product Or Component Type	Multi-mode connector

Complementary

Connector Type	ST
Maximum Insertion Loss	0.53 dB
Minimum Number Of Matings	500 cycles
Cable Outer Diameter	0.9 mm
Product Compatibility	For 50/125 and 62.5/125 µm optical fibre

Environment

Ambient Air Temperature For Operation	-20...80 °C
Product Certifications	UL listed
Standards	ISO/IEC 11081 EIA/TIA-568-B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	6.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	6.72 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications