



Main

Range of product	Digilink
Product or component type	Single-mode connector

Complementary

Connector type	ST
Insertion loss	< 0.3 dB
Number of matings	500 cycles
Cable outer diameter	0.9 mm
Product compatibility	For 9/125 µm optical fibre

Environment

Ambient air temperature for operation	-20...80 °C
Product certifications	UL listed
Standards	EIA/TIA-568-B ISO/IEC 11081

Contractual warranty

Warranty period	18 months
-----------------	-----------