


Product data sheet

Specifications



Cable end, Linergy TR cable ends,
Single conductor, grey, 4mm²,
medium size, markable, insulated,
10 sets of 100

DZ5CA042D

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	DIN 46228-4
Type Of Packing	Bag
Quantity Per Set	10 sets of 100
Cable Cross Section	4 mm ²

Complementary

Cable End Type	Single conductor
Additional Information	For additional marker tag holder
Colour	Grey
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 12
Bezel Size	Ø 5.4 mm
Tube Diameter	3.2 mm
Length	20 mm
Tube Length	10 mm
Cad Overall Depth	20 mm
Net Weight	0.3 kg

Environment

Product Certifications	UL
Ambient Air Temperature For Operation	-20...105 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	1.400 cm
Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	6.000 cm
Package 2 Width	10.000 cm
Package 2 Length	25.000 cm
Package 2 Weight	317.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	5000
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.777 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations