

# Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, white, 0.5mm<sup>2</sup>, for insulated cable, long size, 10 sets of 100

DZ5CE005L10D

## Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Long
Standards	DIN 46228-4
Type Of Packing	String of bags
Quantity Per Set	10 sets of 100
Cable Cross Section	0.5 mm <sup>2</sup>

## Complementary

Cable End Type	Single conductor
Additional Information	Without marker tag holder
Colour	White
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 22
Bezel Size	Ø 3 mm
Tube Diameter	1.4 mm
Length	16 mm
Tube Length	12 mm
Net Weight	0.095 kg

## Environment

Ambient Air Temperature For Operation	-20...105 °C
---------------------------------------	--------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.300 cm
Package 1 Width	0.300 cm
Package 1 Length	1.500 cm
Package 1 Weight	0.100 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	1.000 cm
Package 2 Width	8.500 cm
Package 2 Length	9.000 cm
Package 2 Weight	9.000 g
Unit Type Of Package 3	P06
Number Of Units In Package 3	160000
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	26.928 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Circularity Profile

No need of specific recycling operations