



Main

Range of product	Linery
Product or component type	Cable end
Cable end size	Medium
Standards	DIN 46228-4
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	1 mm ²

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Colour	Red
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 18
Bezel size	Ø 3.5 mm
Tube diameter	1.7 mm
Length	14 mm
Tube length	8 mm
CAD overall width	3 mm
CAD overall height	3 mm
CAD overall depth	14 mm
Product weight	0.1 kg

Environment

Product certifications	UL
------------------------	----

Ambient air temperature for operation	-20...105 °C
---------------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0437 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
