

Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, red, 1mm², for insulated cable, long size, 10 sets of 100

DZ5CE010L12D

Main

| | |
|---------------------------|-------------------|
| Range Of Product | Linergy |
| Product Or Component Type | Cable end |
| Cable End Size | Long |
| Standards | DIN 46228-4 |
| Type Of Packing | String of bags |
| Quantity Per Set | 10 sets of 100 |
| Cable Cross Section | 1 mm ² |

Complementary

| | |
|------------------------|-------------------------------|
| Cable End Type | Single conductor |
| Additional Information | Without marker tag holder |
| Colour | Red |
| Bezel Material | Halogen-free plastic |
| Tube Material | Copper conforming to ISO 1337 |
| Number Of Cables | 1 |
| Awg Gauge | AWG 18 |
| Bezel Size | Ø 3.5 mm |
| Tube Diameter | 1.7 mm |
| Length | 18 mm |
| Tube Length | 12 mm |
| Net Weight | 0.15 kg |

Environment

| | |
|---------------------------------------|--------------|
| Ambient Air Temperature For Operation | -20...105 °C |
|---------------------------------------|--------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 0.400 cm |
| Package 1 Width | 0.400 cm |
| Package 1 Length | 1.400 cm |
| Package 1 Weight | 0.100 g |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 1000 |
| Package 2 Height | 3.000 cm |
| Package 2 Width | 11.000 cm |
| Package 2 Length | 21.000 cm |
| Package 2 Weight | 137.000 g |
| Unit Type Of Package 3 | S01 |
| Number Of Units In Package 3 | 15000 |
| Package 3 Height | 15.000 cm |
| Package 3 Width | 15.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 2.263 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

Certifications & Standards

| | |
|-----------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |