



### Main

Range of product	Linery
Product or component type	Cable end
Cable end size	Long
Standards	DIN 46228-4
Type of packing	Individual bag
Quantity per set	Set of 100
Cable cross section	6 mm <sup>2</sup>

### Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Colour	Yellow
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 10
Bezel size	Ø 6.9 mm
Tube diameter	3.9 mm
Length	26 mm
Tube length	18 mm
Product weight	0.065 kg

### Environment

Product certifications	UL
Ambient air temperature for operation	-20...105 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0437 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------