

# Product data sheet

Specifications



## 13A 3 Pin Switched Socket Outlet with Blue LED, Grey Silver

E3015D\_EBGS

### Main

Range	Neo C-Metro
Product Or Component Type	Socket-outlet
Switch Function	2-pole
Outlet Poles Configuration	3P with shutters
Outlet Standard	MS 589 BS 1363
Bulb Type	LED, blue
Colour Tint	Grey silver

### Complementary

Wiring Device Mounting	Flush Surface
Rated Current	13 A at 250 V AC 50/60 Hz
Material	Brass: contact Copper with silver onlay: bridge Nylon: shutter Polycarbonate: plastic part Steel with brass plating: screws Steel with brass plating: terminals
Load Type	Resistive
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	17 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	BS 1363 MS 589 SS 145

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.7 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	88 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	718 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	8180 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations