

Product data sheet

Specifications



13A Fused Connection Unit, White

E3030FSG_WW

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Neo
Product Or Component Type	Fused connection unit
Colour Tint	White
Standards	BS 1362-4

Complementary

Wiring Device Mounting	Surface Flush
Rated Current	13 A at 250 V AC 50 Hz
Contacts Material	Brass Phosphor bronze
Load Type	Resistive
Protection Type	Fuse
Material	Polycarbonate: grid plate Polycarbonate: surround
Number Of Cables	2 x 4 mm ² input 1 x 1.5 mm ² output 1 x 2.5 mm ² output 3 x 0.5...1.5 mm ² output 3 x 2.5 mm ² input
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	139.5 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information