



Main

Range	Neo
Product or component type	Fused connection unit
Switch function	1-pole
Bulb type	LED with red
Colour tint	Grey silver
Standards	BS 5733

Complementary

Wiring device mounting	Flush Surface
Rated current	10 A, 250 V, AC, 50 Hz
Contacts material	Brass Phosphor bronze
Load type	Resistive
Protection type	Fuse
Material	Polycarbonate with grid plate
Number of cables	2 - cable cross section: 4 mm ² with input
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Contractual warranty

Warranty period	18 months
-----------------	-----------