



Main

Range of product	Neo C-Metro
Product or component type	Fused connection unit
Switch function	1-pole
Colour tint	White
Standards	BS 5733

Complementary

Wiring device mounting	Flush Surface
Rated current	2 A, 250 V, AC, 50 Hz
Contacts material	Phosphor bronze Brass
Load type	Resistive
Protection type	Fuse
Material	Polycarbonate with grid plate Polycarbonate with surround
Number of cables	2 - cable cross section: 4 mm ² with input 1 - cable cross section: 1.5 mm ² with output 1 - cable cross section: 2.5 mm ² with output 3 - cable cross section: 0.5...1.5 mm ² with output 3 - cable cross section: 2.5 mm ² with input
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Contractual warranty

Warranty period	18 months
-----------------	-----------