

# Product data sheet

Specifications



## 3A Fused Connection Unit with Double Pole Switch, White

E3031DFSG3\_WW

⚠ Discontinued on: Jul 20, 2017

⚠ End-of-service on: Dec 15, 2017

⚠ Discontinued

### Main

Range	Neo
Product Or Component Type	Fused connection unit
Switch Function	1-pole
Colour Tint	White
Standards	BS 5733

### Complementary

Wiring Device Mounting	Flush Surface
Rated Current	3 A at 250 V AC 50 Hz
Contacts Material	Phosphor bronze Brass
Load Type	Resistive
Protection Type	Fuse
Material	Polycarbonate: grid plate Polycarbonate: surround
Number Of Cables	2 x 4 mm <sup>2</sup> input 1 x 1.5 mm <sup>2</sup> output 1 x 2.5 mm <sup>2</sup> output 3 x 0.5...1.5 mm <sup>2</sup> output 3 x 2.5 mm <sup>2</sup> input
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications