


Product data sheet

Specifications



13A Fused Connection Unit with Double Pole Switch, Grey Silver

E3031DFSG_GS

 **Discontinued on:** Dec 11, 2019

 **Discontinued**

Main

Range	Neo
Product Or Component Type	Fused connection unit
Switch Function	2-pole
Colour Tint	Grey silver
Standards	BS 1362-4

Complementary

Wiring Device Mounting	Surface Flush
Rated Current	13 A at 250 V AC 50 Hz
Contacts Material	Phosphor bronze Brass
Load Type	Resistive
Protection Type	Fuse
Material	Polycarbonate: grid plate Polycarbonate: surround
Number Of Cables	2 x 4 mm ² input 1 x 1.5 mm ² output 1 x 2.5 mm ² output 3 x 0.5...1.5 mm ² output 3 x 2.5 mm ² input
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.8 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	129.5 g

Contractual warranty

Warranty	18 months
----------	-----------