



### Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Flush Surface
Switch function	Momentary
Switch application	Switch
Bulb type	Fluorescent with green
Colour tint	Grey silver

### Complementary

Rated current	100 mA, 24 V, DC
Number of gangs	1 gang horizontal
Material	Brass terminals Polycarbonate plastic part
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23 mm
Depth	36 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications