



Main

Range	Neo
Wiring device mounting	Flush Surface
Switch function	1-way
Switch application	Switch
Load type	Fluorescent lamp Incandescent lamp Inductive Resistive
Bulb type	Fluorescent with green
Colour tint	Grey silver

Complementary

Rated current	10 A, 250 V, AC, 50/60 Hz
Number of gangs	1 gang horizontal
Material	Brass metal parts Polycarbonate plastic part Steel metal parts
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23.5 mm
Depth	36 mm

Environment

Ambient air temperature for operation	0...40 °C
---------------------------------------	-----------

Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	EN 60669-1 GB 16915.1 IEC 60669-1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations