

Product data sheet

Specifications



20A Horizontal Dolly Double Pole Switch with White LED, White

E3031HD20_EWWW

Main

Range	Neo
Product Or Component Type	Control switch
Device Application	Control
Wiring Device Mounting	Flush Surface
Switch Function	2-pole
Switch Application	Switch
Load Type	Resistive Inductive Fluorescent lamp
Bulb Type	LED (white)
Colour Tint	White

Complementary

Rated Current	20 AX at 250 V AC 50/60 Hz
Number Of Gangs	1 gang horizontal
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping Connection Capacity	1 x 2.5...1 x 6 mm ² for solid cable(s) 1 x 2.5...1 x 6 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	19.7 mm
Depth	33.1 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	EN 60669-1 GB 16915.1 IEC 60669-1

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	32.5 cm
Package 1 Length	50.0 cm
Package 1 Weight	132.325 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information