

# Product data sheet

Specifications



## 16AX Intermediate Horizontal Switch w/ Green Fluorescent Indicator, White

E3031HIA\_FWWW

 **Discontinued on:** Jan 29, 2016

 **Discontinued**

### Main

Range	Neo
Wiring Device Mounting	Flush Surface
Switch Function	Intermediate
Switch Application	Switch
Load Type	Resistive Fluorescent lamp Inductive
Bulb Type	Fluorescent (white)
Colour Tint	White

### Complementary

Rated Current	16 AX at 250 V AC 50 Hz 20 A at 250 V AC 50 Hz
Number Of Gangs	1 gang horizontal
Material	Brass: metal parts Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23.5 mm
Depth	36 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	SS 227 IEC 60669-1 MS 616

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	121.325 g

## Contractual warranty

Warranty	18 months
----------	-----------