

Product data sheet

Specifications



10AX "DoNotDisturb" Horizontal Control Switch w /Illuminated Symbol, Grey Silver

E3031HPDND_GS

⚠ Discontinued on: Jan 1, 2006

⚠ Discontinued

Main

Range	Neo
Product Or Component Type	Control switch
Wiring Device Mounting	Surface Flush
Switch Function	1-way
Switch Application	Switch
Load Type	Resistive Inductive Fluorescent lamp Incandescent lamp
Colour Tint	Grey silver

Complementary

Rated Current	10 AX at 250 V AC 50/60 Hz
Number Of Gangs	1 gang horizontal
Material	Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s) 4 x 1.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	24.2 mm
Depth	37.3 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	GB 16915.1 IEC 60669-1 EN 60669-1

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	92.59 g

Contractual warranty

Warranty	18 months
----------	-----------