



Main

Range	Neo
Product or component type	Connection unit
Colour tint	White
Standards	BS 5733

Complementary

Wiring device mounting	Flush Surface
Rated current	25 A
Number of cables	1 - cable cross section: 4 mm ² with input 1 - cable cross section: 4 mm ² with output 1 - cable cross section: 2.5 mm ² with output (flexible)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
