


# Product data sheet

Specifications



## 1 WAY BELL PRESS SWITCH VERTICAL, WHITE

E3031VBP\_WW\_G19

 **Discontinued on:** Dec 11, 2019

 **Discontinued**

### Main

Range	Neo
Wiring Device Mounting	Surface Flush
Switch Function	Momentary
Switch Application	Bell
Load Type	Inductive Resistive
Bulb Type	Fluorescent (white)
Colour Tint	White

### Complementary

Rated Current	4 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang vertical
Material	Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23 mm
Depth	36 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	GB 16915.1 EN 60669-1 IEC 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications