

# Product data sheet

Specifications



## 20A Vertical Dolly Double Pole Switch with White LED, Grey Silver

E3031VD20\_EBGS

### Main

Range	Neo
Product Or Component Type	Control switch
Wiring Device Mounting	Surface Flush
Switch Function	2-pole
Switch Application	Switch
Load Type	Inductive Fluorescent lamp Resistive
Bulb Type	LED (blue)
Colour Tint	Grey silver

### Complementary

Rated Current	20 A at 250 V AC 50 Hz
Number Of Gangs	1 gang vertical
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping Connection Capacity	1 x 2.5...1 x 6 mm <sup>2</sup> for solid cable(s) 1 x 2.5...1 x 6 mm <sup>2</sup> for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	86 mm
Height	86 mm
Embedding Depth	19.7 mm
Depth	8 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	GB 16915.1 EN 60669-1 IEC 60669-1

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	117.425 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	939 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	9394 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	<a href="#">End of Life Information</a>