



### Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Flush Surface
Switch function	Intermediate
Switch application	Switch
Load type	Fluorescent lamp Inductive Resistive
Bulb type	LED with blue
Colour tint	Grey silver

### Complementary

Rated current	16 AX, 250 V, AC, 50 Hz 20 A, 250 V, AC, 50 Hz
Number of gangs	1 gang vertical
Material	Brass metal parts Polycarbonate plastic part
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23.5 mm
Depth	36 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	IEC 60669-1 MS 616 SS 227

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------