

# Product data sheet

Specifications



## 16AX Intermediate Vertical Switch with Green Fluorescent Indicator, Grey Silver

E3031VIA\_FGGS

⚠ Discontinued on: Jan 29, 2016

⚠ Discontinued

### Main

Range	Neo
Product Or Component Type	Control switch
Wiring Device Mounting	Flush Surface
Switch Function	Intermediate
Switch Application	Switch
Load Type	Fluorescent lamp Inductive Resistive
Bulb Type	Fluorescent (green)
Colour Tint	Grey silver

### Complementary

Rated Current	16 AX at 250 V AC 50 Hz 20 A at 250 V AC 50 Hz
Number Of Gangs	1 gang vertical
Material	Brass: metal parts Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23.5 mm
Depth	36 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	SS 227 IEC 60669-1 MS 616

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	120.225 g

## Contractual warranty

Warranty	18 months
----------	-----------