

Product data sheet

Specifications



16AX Intermediate Vertical Switch with White Fluorescent Indicator, White

E3031VIA_FWXX

⚠ Discontinued on: Jan 29, 2016

⚠ Discontinued

Main

Range	Neo
Product Or Component Type	Control switch
Wiring Device Mounting	Flush Surface
Switch Function	Intermediate
Switch Application	Switch
Load Type	Fluorescent lamp Inductive Resistive
Bulb Type	Fluorescent (white)
Colour Tint	White

Complementary

Rated Current	16 AX at 250 V AC 50 Hz 20 A at 250 V AC 50 Hz
Number Of Gangs	1 gang vertical
Material	Brass: metal parts Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23.5 mm
Depth	36 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	SS 227 MS 616 IEC 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	120.225 g

Contractual warranty

Warranty	18 months
----------	-----------