


Product data sheet

Specifications



2 Gang Dimming Control Wallplate with Amber LED, Grey Silver

E3032DLV_EAGS

 **Discontinued on:** Dec 31, 2018

 **Discontinued**

Main

Range	Neo ELV+
Product Or Component Type	Switch
Switch Application	Dimming up/down control
Colour Tint	Grey silver

Complementary

Connector Type	RJ45 5e)
Output Type	Voltage free dry contact
Rated Current	20 mA at < 24 V DC
Status Led	Amber LED
Number Of Gangs	2 gangs horizontal
Width	87 mm
Height	87 mm
Embedding Depth	20.3 mm
Depth	35 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	90.717 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications