



Main

Product or component type	Data socket
Data socket type	RJ45 - 8 contacts - category 5e
Colour tint	Grey silver

Complementary

Rated current	1.5 A
Socket number	2
Insulation resistance	≥ 200 mOhm
Contact resistance	≤ 1000 μ Ohm
Number of gangs	2 gangs
Return loss	≥ 23 dB
AWG gauge	AWG 26...AWG 22 for 4 twisted pair cables
Contacts material	Phosphor bronze with gold plating contact Phosphor bronze with nickel plating IDC contact
Material	Polycarbonate plastic part
Device mounting	Surface Flush
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric strength	1000 V for 60 s at 60 Hz
Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	ISO/IEC 11801 EIA/TIA 568 FCC part 68 YD/T 577-92

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
