



Main

Product or component type	Telephone socket
Telephone socket type	RJ11 4 3
Colour tint	White

Complementary

Wiring device mounting	Flush Surface
Socket number	2
Rated current	1.5 A 125 Vrms AC
Number of gangs	2 gangs
Material	PBT 15 % FG insert PC housing Polycarbonate plastic part
Contacts material	Phosphor bronze contact Phosphor bronze with tin plating IDC contact
Contact resistance	$\leq 1000000 \mu\text{Ohm}$
Insulation resistance	$\geq 1000 \text{ MOhm}$
AWG gauge	AWG 26...AWG 24 2 twisted pair cables
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric strength	750 V 60 s 60 Hz
Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	YD/T 577-92

Contractual warranty

Warranty period	18 months
-----------------	-----------