



Main

Product or component type	USB charger
Fixing mode	Screw

Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	White
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	2 modules 46 x 36.7 x 21.7 mm
Condition of use	Room temperature
Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	PA (polyamide) 6 for housing Silicone rubber for cover PC (polycarbonate) for grid plate
Shape of screw head	Cross
Number of terminals	2 screw terminals
Clamping connection capacity	2.5 mm ² (stranded) 2.5 mm ² (flexible) 2.5 mm ² (rigid) 1.5 mm ² (stranded) 1.5 mm ² (flexible) 1.5 mm ² (rigid)
Wire stripping length	6 mm
Product compatibility	Apple Samsung HW XiaoMi HTC Major smart phone and tablet Power bank
Standards	IEC 60950-1 GB 4943.1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

MS IEC 60950-1
CNS 14336
CNS 13438

Height	87 mm
Width	87 mm
Depth	39 mm
Embedding depth	29.3 mm
Product weight	0.097 kg

Environment

Product certifications	CCC IEC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap
Environmental health and issues	Halogen free